



MANUAL

WELDAS PRODUCT: 10-2385

Weldas CE markings on this glove designates it as tested and certified according to directive 89/686/EEC Level 2.

EN12477, 09.2005 Type A

Glove type: welding glove

Trade mark: **COMFOflex**

Size: see imprint on glove

Sizing according to EN 12477, 2005 / EN 420, 2003

Hand Size Index	9	9½	10½
Weldas Size Label	L	XL	XXL
Measurement in mm	229	241	267
Total length of glove in mm	370	370	370




Health information:

The pH, Chromium (VI) and PCP levels of all materials have been tested and meet CE health standards.

Coloring: coloring is done by using natural materials

The following explains the pictograms marked on the glove:

Protective gloves against mechanical risks



4133

Digit	Test Resistance	Level 1	Level 2	Level 3	Level 4	Level 5
1st	Abrasion (# cycles)	100	500	2000	8000	—
2nd	Blade cut (index)	1,2	2,5	5,0	10,0	20,0
3rd	Tear (Newton)	10	25	50	75	—
4th	Puncture (Newton)	20	60	100	150	—

Protective gloves against thermal risks



41344X

Digit	Test resistance	Digit	Test Resistance
1st	Burning behaviour	5th	Small splashes of molten metal
2nd	Contact heat	6th	Large quantities of molten metal
3rd	Convective heat		
4th	Radiant heat		

!!! If indication on product is "X" : than the indicated position has not been tested !!!

EN12477, 09.2005: Protective gloves for welders (minimum requirements)

Requirements	EN	Type A		Type B	
		Minimum Rating		Minimum Rating	
Electrical Insulation	pr1149-2		R≥10 ⁶ Ω		R≥10 ⁵ Ω
Abrasion Resistance	EN388	2	500 cycles	1	100 cycles
Blade Cut Resistance	EN388	1	Index 1,2	1	Index 1,2
Tear Resistance	EN388	2	25 N	1	10 N
Puncture Resistance	EN388	2	60 N	1	20 N
Burning Behaviour	EN407	3		2	
Contact Heat Resistance	EN407	1	100 C	1	100 C
Convective Heat Resistance	EN407	2	HTI≥7	0	
Small Molten Splash Resistance	EN407	3	25 Droplets	2	15 Droplets
Dexterity (pick up of rod dia.)	EN420	1	≤1mm	4	≤6,5mm

Instruction for use:

This glove is intended to be used as a welding glove for MIG/MAG as well as electrode welding. The aluminized back has the function the reflect a radiation and/or heat source

Warranty: This product is warranted against manufacturing defects. Because applications vary, it is the user's responsibility to identify the right product for each application.

Washing, drying and ironing:

No bleach or acid should be used, just standard washing detergents. The characteristics of the leather will change after 1 or 2 washings, hardening of the leather is typical after washing.

Mechanical drying and ironing is possible but not advised

UV:

Within this norm there is no test method indicated on UV radiation but, normally, this will give no problem with these materials used.

Electrical danger:

These products can pass on electrical currents, risk is higher when the product is wet !

Materials used:

An Aluminized back of PFR Rayon with a split deer-skin layer and a **COMFOflex** lining for the back. The palm side of the glove is made of thick, pliable and durable side split cowhide also with COMFOflex lining. The cuff is lined with a flame retardant fabric for extra safety. It is 4 ply Dupont KEVLAR[®] sewn for added durability. All seams are fully welded.

DuPont™ and KEVLAR[®] are trademarks or registered trademarks of E.I.duPont de Nemours and Company, **COMFOflex** is a registered trademark of Weldas company

Storage: Store dry and at temperatures over 5° Celcius. Do not stack higher than 5 cartons on 1 pallet

Caution: Weldas gloves and clothing have been tested and certified at TÜV Rheinland LGA Products GmbH, Germany (EU no. 0197).

For more information on EN standards, testing methods, test reports, product certifications, and other products, please e-mail us at: europe@weldas.com or visit our web site: www.weldas.com

Manufacturer of this product is: Weldas.

Address information Weldas:

European office:

Weldas Europe B.V.
Blankenweg 18 4612 RC Bergen op Zoom Holland
E-mail: europe@weldas.com

Head office Weldas worldwide as well as USA office:

Weldas Company
128 Seabord Lane Franklin TN 37067 USA
E-mail: info@weldas.com